

Rittal – The System.

Faster – better – everywhere.



SZ 2488.000

Závitorezné skrutky

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2488.000 - Závitorezné skrutky

For the round holes 4.5 mm diameter in the enclosure section, punched rails and punched sections without mounting flanges.

Features

Obj. č.	SZ 2488.000
Prevedenie	Skrutky so zapustenou hlavou
Oblasti použitia	Pre kruhové otvory s priemerom 4,5 resp. 4,7 mm v profile skrine, montážnych lištách a montážnych chassis
Rozmery	Závit: M5 Dĺžka závit: 12 mm
Závit	M5
Balenie	500 pc(s).
Netto hmotnosť	0,5 kg
Brutto hmotnosť	0,844 kg
Číslo colnej sadzby	73181900
ETIM 9	EC000891
ETIM 8	EC000891
ECLASS 8.0	23110117
Popis výrobku	SZ skrutky so zapustenou hlavou, pre závit M5, závitorezné