

Rittal – The System.

Faster – better – everywhere.



AX 2509.010

Transportné oká

State: 13.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2509.010 - Transportné oká pre AX, AE

For crane transportation of enclosures, with reinforcement plate to be inserted underneath.



Features

Obj. č.	AX 2509.010
Rozsah dodávky	Transportné oká Plechová vystužovacia doska
Rozmery	Závit: M12
Type rating podľa UL 50E	Type 1 Type 12
Vhodné pre	Typ skrine: AX AE
Balenie	2 pc(s).
Netto hmotnosť	0,62 kg
Brutto hmotnosť	0,66 kg
PCF per pack (cradle-to-gate)	2,5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73182900
ETIM 9	EC002621
ETIM 8	EC002621
ECLASS 8.0	27189262
Popis výrobku	Transportné oká AXE

Approvals

Approvals

UL + C-UL - FTTA