

Rittal – The System.

Faster – better – everywhere.



SZ 2565.200

Plastová prírubová doska, modulárna

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2565.200 - Plastová prírubová doska, modulárna s metrickým predlisovaným otvorom, pre AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).



Features

Obj. č.	SZ 2565.200
Materiál	plast podľa normy UL 94-V0
Farba	RAL 7035
Number of rectangular cutouts information	1 hranatý výrez na umiestnenie 10 tesniacich vložiek, malý
Number of rectangular cutouts	5
Poznámka	Priradenie veľkosti príruby nájdete pri príslušných skrinách.
Počet zoslabených miest na vyrazenie metrických otvorov	4 x M12 4 x M16 4 x M20 3 x M25 1 x M32 1 x M40
Rozmery	Šírka: 301 mm Hĺbka: 221 mm
Vhodné pre	Typ skrine: AX

Features

Prírubová doska	Veľkosť: 5
Rozsah prevádzkových teplôt	-40 °C...80 °C
Stupeň krytia IP podľa normy EN 60 529	IP 66 if installed correctly
Type rating podľa UL 50E	Type 1 Type 12
Balenie	1 pc(s).
Netto hmotnosť	0,4 kg
Brutto hmotnosť	0,418 kg
Číslo colnej sadzby	39269097
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Popis výrobku	Plastová prírubová doska SZ, modulárna s metrickými predvyrazenými otvormi, pre AX, ŠxH: 301 x 221 mm

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------