


Rittal – The System.

Faster – better – everywhere.



SZ 2567.400 Prírubová doska

State: 9.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2567.400 - Prírubová doska s pružným zvieracím profilom, pre AX

For feeding through pre-fabricated cables when the gland plate has already been fitted to the enclosure. Split gland plates can be sealed using movable plates with a foam rubber cable clamp strip.

Features

Obj. č.	SZ 2567.400
Materiál	Prírubová doska: oceľový plech
Farba	RAL 7035
Rozmery	Šírka: 436 mm Hĺbka: 221 mm
Vhodné pre	Typ skrine: AX
Prírubová doska	Veľkosť: 7
Balenie	1 pc(s).
Netto hmotnosť	2 kg
Brutto hmotnosť	2,034 kg
Číslo colnej sadzby	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Popis výrobku	SZ kovová prírubová doska, pre AX, s elastickým upínacím profilom, ŠxH: 436x221 mm, pre prírubové dosky veľkosti 7