

Rittal – The System.

Faster – better – everywhere.



SZ 2577.010

Plastové rukoväte

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2577.010 - Plastové rukoväte pre otočné uzávery

As an alternative to the standard lock insert with or without lock cylinder insert. For use in accordance with the project-specific approved-material lists for the relevant brand.

Features

Obj. č.	SZ 2577.010
Prevedenie	A
Materiál	Skriňa z plastu spevneného sklenými vláknami Uzáver: plast Tesnenie: PU Upínací diel: ocel'ový plech, pozinkovaný
Farba	RAL 9011
Rozsah dodávky	Dodáva sa bez kľúčov. Plastová rukoväť Tesnenie Upínací diel Uzáver AX Uzáver KX Upevňovacia skrutka
Poznámka	Iné zámky na vyžiadanie.
Poznámka k obj. č.	Pri zámku E1 je možné kľúč vytiahnuť len v zamknutom stave. To znamená, že pre skriňu je možné použiť len jednu plastovú rukoväť 2577.010. Pre prípadný druhý otočný uzáver je možné potom použiť plastovú rukoväť 2533.100 bez zámku.
Uzáver	Vložka uzáveru: Zámok E1
Balenie	1 pc(s).
Netto hmotnosť	0,111 kg
Brutto hmotnosť	0,111 kg
Číslo colnej sadzby	39269097
ETIM 9	EC000327
ETIM 8	EC000327

Features

ECLASS 8.0

27409217

Popis výrobku

Plastová rukoväť SZ pre AX a KX, s bezpečnostnou vložkou, zámok E1