

# Rittal – The System.

Faster – better – everywhere.



## AX 2580.004 Tesniaca vložka

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2580.004 - Tesniaca vložka pre prírubovú dosku z plastu, modulárny a tesniaci rám, modulárny

The slotted seal inserts, in conjunction with the inlays, allow individual cable entry, even with preassembled cables.

## Features

|                          |  |
|--------------------------|--|
| Obj. č.                  | AX 2580.004  |
| Prevedenie               | Malá tesniaca vložka   |
| Materiál                 | Plast  |
| Farba                    | RAL 7035   |
| Type rating podľa UL 50E | Type 1<br>Type 12<br>Type 4X indoor use only   |
| Pre priemer kábla        | 4 mm   |
| Balenie                  | 10 pc(s).  |
| Netto hmotnosť           | 0,03 kg  |
| Brutto hmotnosť          | 0,075 kg   |
| Číslo colnej sadzby      | 40082900   |
| ETIM 9                   | EC000441   |
| ETIM 8                   | EC000441   |
| ECLASS 8.0               | 27149109   |
| Popis výrobku            | SZ tesniace vložky, pre plastovú prírubovú dosku, modulárne a tesniaci rám modulárny, malý, pre priemer kábla 4 mm |

## Approvals

|           |                        |
|-----------|------------------------|
| Approvals | UR + C-UR (recognized) |
|-----------|------------------------|