


Rittal – The System.

Faster – better – everywhere.



AX 2580.011 Tesniaca vložka

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2580.011 - Tesniaca vložka pre prírubovú dosku z plastu, modulárny a tesniaci rám, modulárny

The slotted seal inserts, in conjunction with the inlays, allow individual cable entry, even with preassembled cables.

Features

Obj. č.	AX 2580.011
Prevedenie	Malá tesniaca vložka
Materiál	Plast
Farba	RAL 7035
Type rating podľa UL 50E	Type 1 Type 12 Type 4X indoor use only
Pre priemer kábla	11 mm
Balenie	10 pc(s).
Netto hmotnosť	0,01 kg
Brutto hmotnosť	0,06 kg
Číslo colnej sadzby	40082900
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Popis výrobku	SZ tesniace vložky, pre plastovú prírubovú dosku, modulárne a tesniaci rám modulárny, malý, pre priemer kábla 11 mm

Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------