

# Rittal – The System.

Faster – better – everywhere.



## AX 2580.120 Tesniaca vložka

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2580.120 - Tesniaca vložka pre prírubovú dosku z plastu, modulárny a tesniaci rám, modulárny

The slotted seal inserts, in conjunction with the inlays, allow individual cable entry, even with preassembled cables.

## Features

Obj. č.	AX 2580.120
Prevedenie	Veľká tesniaca vložka
Materiál	Plast
Farba	RAL 7035
Type rating podľa UL 50E	Type 1 Type 12 Type 4X indoor use only
Pre priemer kábla	20 mm
Balenie	5 pc(s).
Netto hmotnosť	0,1 kg
Brutto hmotnosť	0,145 kg
Číslo colnej sadzby	40082900
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Popis výrobku	SZ tesniace vložky, pre plastovú prírubovú dosku, modulárne a tesniaci rám modulárny, veľké, pre priemer kábla 20 mm

## Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------