

Rittal – The System.

Faster – better – everywhere.



AX 2583.100

Tesniaci rám, modulárny

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2583.100 - Tesniaci rám, modulárny

For the universal use on all surfaces and walls, for feeding through pre-fabricated cables with connectors. Can also be mounted onto 24-pole or 16-pole connector cut-outs.

Features

Obj. č.	AX 2583.100
Prevedenie	Pre 10 malých tesniacich vložiek
Materiál	Plast
Farba	Čierna
Rozsah dodávky	Tesniaci rám Zaistovacie rám
Potrebný výrez	113.5 x 46 mm (24-pole)
Rozmery	Šírka: 153,08 mm Hĺbka: 70,08 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 66
Balenie	1 pc(s).
Netto hmotnosť	0,12 kg
Brutto hmotnosť	0,14 kg
Číslo colnej sadzby	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Popis výrobku	Tesniaci rám SZ, modulárny, pre 10 malých tesniacich vložiek alebo pre 24-vodičové výrezy konektorov

Approvals

Approvals

Approvals

UR + C-UR (recognized)