

Rittal – The System.

Faster – better – everywhere.



AX 2584.100 Upevnenie na stípe

State: 28.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2584.100 - Upevnenie na stĺpe pre nástennú skrinku AX, KX, AX z plastu, AX IT, CS

For reliable, convenient fastening to round or square poles.



Features

Obj. č.	AX 2584.100
Technické údaje	Pre priemer stĺpa: Ø od 40 do 170 mm Pre veľkosť stĺpa: □ od 50 do 150 mm
Materiál	Profilové lišty, upínací profil: oceľový plech Upínací pásik: nerezová oceľ 1.4301 (AISI 304)
Povrch	Mounting angle, clamp strip: Galvanic zinc-nickel, passivated
Rozsah dodávky	2 profilové lišty, dĺžka 600 mm 4 upínacie profily 2 sťahovacie pásy 4 upínacie uholníky 4 samorezné skrutky M10 pre montáž na skriňu
Poznámka	Vhodné iba pre skrine do šírky 600 mm.
Vhodné pre	Typ skrine: AX KX AX plastic AX IT CS wall-mounted enclosures AX outdoor housing AE KL EB AX wall-mounted enclosure, 3-part

Features

Type rating podľa UL 50E	Type 1 Type 3R Type 4 Type 12
Balenie	2 pc(s).
Netto hmotnosť	1,88 kg
Brutto hmotnosť	1,96 kg
PCF per pack (cradle-to-gate)	7,3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	83024900
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Popis výrobku	Upevnenie na stĺp AX

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------