


Rittal – The System.

Faster – better – everywhere.



FT 2793.560 Priehľadové okno

Source: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2793.560 - Priehľadové okno Nerezová oceľ

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access. Made from stainless steel 1.4301 (AISI 304).



Features

Obj. č.	FT 2793.560
Materiál	Nerezová oceľ 1.4301 (AISI 304) Jednovrstvové bezpečnostné sklo
Rozsah dodávky	Vrátane upevňovacieho materiálu
Stupeň krytia IP podľa normy EN 60 529	IP 54
Poznámka	Sériová uzatváracia vložka typu Doppelbart, zameniteľná za uzatváracie vložky 27 mm, prevedenie A a/alebo za uzatvárací systém Ergoform S (okrem V=270 mm)
Rozmery	Šírka: 522 mm Výška: 600 mm Hĺbka: 38 mm
Priehľadová plocha	Šírka priehľadového okna: 408 mm Výška priehľadového okna: 543 mm
Montážna hĺbka pre komponenty (max.)	31 mm

Features

Balenie	1 pc(s).
Netto hmotnosť	6,175 kg
Brutto hmotnosť	6,5 kg
Číslo colnej sadzby	76101000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Popis výrobku	Presklené okienko FT, ŠxVxH 522x600x38 mm, nehrdzavejúca oceľ, 1.4301