


Rittal – The System.

Faster – better – everywhere.



AX 2820.081

Rohový diel podstavca s krytmi podstavca vpredu a vzadu, 100 mm

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2820.081 - Rohový diel podstavca s krytmi podstavca vpredu a vzadu, 100 mm pre AX

Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

Features

Obj. č.	AX 2820.081
Materiál	Rohový diel podstavca: ocelový plech Kryt podstavca vpredu/vzadu: ocelový plech Rohová krytka: plast
Farba	RAL 9005
Rozsah dodávky	4 rohové diely podstavca, výška 100 mm 4 rohové kryty 2 kryty podstavca vpredu/vzadu, výška 100 mm Vrátane upevňovacieho materiálu
Poznámka	Kryty podstavca, pre bočné uzavretie jednotky podstavca Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Rozmery	Výška: 100 mm
Vhodné pre	Typ skrine: AX Šírka: = 800 mm
Type rating podľa UL 50E	Type 1 Type 3R Type 4 Type 12
Balenie	2 pc(s).
Netto hmotnosť	4,7 kg
Brutto hmotnosť	5,1 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000721

Features

ETIM 8	EC000721
ECLASS 8.0	27182003
Popis výrobku	AX rohové diely podstavca s krytom podstavca, vpredu a vzadu, V: 100 mm, pre Š: 800 mm

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------
