

# Rittal – The System.

Faster – better – everywhere.



## AX 2820.122

# Rohový diel podstavca s krytmi podstavca vpredu a vzadu, 200 mm

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2820.122 - Rohový diel podstavca s krytmi podstavca vpredu a vzadu, 200 mm pre AX

Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

## Features

Obj. č.	AX 2820.122
Materiál	Rohový diel podstavca: ocelový plech Kryt podstavca vpredu/vzadu: ocelový plech Rohová krytka: plast
Farba	RAL 9005
Rozsah dodávky	4 rohové diely podstavca, výška 200 mm 4 rohové kryty 1 kryt podstavca, vpredu/vzadu, 200 mm 2 kryty podstavca vpredu/vzadu, výška 100 mm Vrátane upevňovacieho materiálu
Poznámka	Kryty podstavca, pre bočné uzavretie jednotky podstavca Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Rozmery	Výška: 200 mm
Vhodné pre	Typ skrine: AX Šírka: = 1.200 mm
Type rating podľa UL 50E	Type 1 Type 3R Type 4 Type 12
Balenie	2 pc(s).
Netto hmotnosť	11,5 kg
Brutto hmotnosť	11,58 kg
Číslo colnej sadzby	94039910

# Features

---

ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Popis výrobku	AX rohové diely podstavca s krytom podstavca, vpredu a vzadu, V: 200 mm, pre Š: 1200 mm

# Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------