


# Rittal – The System.

Faster – better – everywhere.



## AX 2820.310

## Bočnice podstavca, 100 mm

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2820.310 - Bočnice podstavca, 100 mm pre AX

To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

## Features

|                          |   |
|--------------------------|---|
| Obj. č.                  | AX 2820.310   |
| Materiál                 | Oceľový plech   |
| Farba                    | RAL 9005  |
| Rozsah dodávky           | Vrátane upevňovacieho materiálu   |
| Poznámka                 | Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system |
| Rozmery                  | Výška: 100 mm   |
| Vhodné pre               | Typ skrine: AX<br>Hĺbka: = 300 mm   |
| Type rating podľa UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 12  |
| Balenie                  | 2 pc(s).  |
| Netto hmotnosť           | 0,66 kg   |
| Brutto hmotnosť          | 0,667 kg  |
| Číslo colnej sadzby      | 94039910  |
| ETIM 9                   | EC000721  |
| ETIM 8                   | EC000721  |
| ECLASS 8.0               | 27182003  |
| Popis výrobku            | Kryty podstavca AX, bočné, výška: 100 mm, pre hĺbku: 300 mm   |

# Approvals

---

Approvals

UL + C-UL - FTTA