

# Rittal – The System.

Faster – better – everywhere.



## AX 2820.410

## Bočnice podstavca, 100 mm

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2820.410 - Bočnice podstavca, 100 mm pre AX

To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

## Features

Obj. č.	AX 2820.410
Materiál	Oceľový plech
Farba	RAL 9005
Rozsah dodávky	Vrátane upevňovacieho materiálu
Poznámka	Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Rozmery	Výška: 100 mm
Vhodné pre	Typ skrine: AX Hĺbka: = 400 mm
Type rating podľa UL 50E	Type 1 Type 3R Type 4 Type 12
Balenie	2 pc(s).
Netto hmotnosť	1,04 kg
Brutto hmotnosť	1,054 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Popis výrobku	Kryty podstavca AX, bočné, výška: 100 mm, pre hĺbku: 400 mm

# Approvals

---

Approvals

UL + C-UL - FTTA