


Rittal – The System.

Faster – better – everywhere.



SZ 2899.320

Gumová priechodka

State: 11.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2899.320 - Gumová priechodka Na hrúbky steny 1,5 až 4,5 mm

For cable entry, simply cut off at the required level to match the cable diameter.



Features

Obj. č.	SZ 2899.320
Oblasti použitia	Na hrúbky steny 1,5 až 4,5 mm
Materiál	Vložka/plášť: termoplastický elastomér
Rozmery	Závit: M32
Na hrúbku steny (max.)	1,5 - 4,5 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 54 with careful cable entry
Pre Ø kábla	13 - 26,5 mm
Balenie	25 pc(s).
Netto hmotnosť	0,1 kg
Brutto hmotnosť	0,144 kg
Číslo colnej sadzby	39269097
ETIM 9	EC000879
ETIM 8	EC000879
ECLASS 8.0	27069216
Popis výrobku	SZ priechodková vložka, pre hrúbky steny od 1,5 do 4,5 mm, pre otvor M32, rozsah tesnenia: 13-26,5 mm