


# Rittal – The System.

Faster – better – everywhere.



## SK 3145.000

# Tlačné ventilátory pre 482,6 mm (19")

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3145.000 - Tlačné ventilátory pre 482,6 mm (19")

## Množstvo vzduchu 320 m<sup>3</sup>/h

2 U tangential fan with up to 320 m<sup>3</sup>/h air throughput. The minimal noise generation of 52 dB makes it suitable for use in office environments.

## Features

Obj. č.	SK 3145.000
Farba	RAL 9005
Rozsah dodávky	Kompletné zariadenie pripravené na okamžité pripojenie a použitie Filtrovaná vložka
Počet otáčok	2 245 rpm
Menovité prevádzkové napätie	115 V, 1~, 50 Hz/60 Hz
Menovitý elektrický príkon Pel	Pri 50 Hz: 37 W Pri 60 Hz: 46 W
Menovitý prúd max.	Pri 50 Hz: 0,32 A
Rozmery	Šírka: 482,6 mm Výška: 88 mm Hĺbka: 158 mm
Hladina akustického tlaku	Pri 50 Hz: 52 dB(A) Pri 60 Hz: 62 dB(A)
Max. statický rozdiel tlakov	65 - 70 Pa
Rozsah prevádzkových teplôt	-10 °C...55 °C
Vnútorň okruh pri 50 Hz	320 m <sup>3</sup> /h
Vnútorň okruh pri 60 Hz	330 m <sup>3</sup> /h
Balenie	1 pc(s).
Netto hmotnosť	2,3 kg
Brutto hmotnosť	2,388 kg
Číslo colnej sadzby	84145915

## Features

---

ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Popis výrobku	SK radiálny ventilátor, 320 m <sup>3</sup> /h, 115 V, 50/60 Hz, ŠxVxH: 482,6x88x158 mm, 19" inštalácia

## Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------