


**Rittal – The System.**

Faster – better – everywhere.



**SK 3174.100**

**Filtračná vložka z netkanej textílie**

State: 21.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3174.100 - Filtračná vložka z netkanej textílie

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

Obj. č.	SK 3174.100
Prevedenie	pre strešné ventilátory
Materiál	Chemické vlákna
Poznámka	Výkonové parametre, stupeň krytia a certifikácie prístrojov sú zaručené len v spojení s originálnymi filtračnými vložkami Rittal.
Vhodný pre obj. č.	3138.... 3139.... 3140....
Rozmery	Šírka: 264 mm Výška: 95 mm Hĺbka: 17 mm
Trieda filtra	podľa STN EN 779: G3
Stupeň krytia IP podľa normy IEC 60 529	IP 55 in roof-mounted fans
Balenie	12 pc(s).
Netto hmotnosť	0,012 kg
Brutto hmotnosť	0,1 kg
Číslo colnej sadzby	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	SK náhradná filtračná vložka, do strešných ventilátorov, za SK 3138./3139./3140. ŠxVxH 264 x 95 x 17 mm

# Approvals

---

Approvals

CSA

UR + C-UR (recognized)