


# Rittal – The System.

Faster – better – everywhere.



## SK 3201.840

# Modulárne chladiace dvere pre klimatizačný modul VX25

State: 28.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3201.840 - Modulárne chladiace dvere pre klimatizačný modul VX25 pre vstavanie

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX.

## Features

Obj. č.	SK 3201.840
Materiál	Oceľový plech
Farba	RAL 7035
Rozsah dodávky	Chladiace dvere bez predmontovaného chladiaceho modulu 180° Pánty, uhol otvorenia dverí cca 130°
Poznámka k obj. č.	Vhodné pre skrine VX Pri skrinách VX so šírkou 1 200 mm je možné použiť ako druhé dverné krídlo existujúce otočné dvere – nezávisle na pozícii prístroja vľavo alebo vpravo Pánty dverí vľavo
Vhodné pre	Chladiaci modul vľavo
Vhodné pre	Typ skrine: VX: = 600 mm: = 1.800 mm Typ skrine: = 1.200 mm
Balenie	1 pc(s).
Netto hmotnosť	25,7 kg
Brutto hmotnosť	26,8 kg
Číslo colnej sadzby	94039910
ETIM 9	EC002510
ETIM 8	EC002510
ECLASS 8.0	27180702
Popis výrobku	Chladiace dvere pre chladiaci modul, pre VX šírka 600/1200 mm, výška 1800 mm

# Approvals

---

Explanations

Declaration of conformity - F-gas regulation