


# Rittal – The System.

Faster – better – everywhere.



## SK 3237.055

# Filtračná vložka z netkanej textílie

State: 28.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3237.055 - Filtračná vložka z netkanej textílie

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

Obj. č.	SK 3237.055
Prevedenie	pre ventilátory s filtrom
Materiál	Chemické vlákna
Farba	biela
Poznámka	Nie je vhodný pre EMC ventilátory s filtrom/výstupné mriežky.
Vhodný pre obj. č.	3237.3xx/3237.7xx
Rozmery	Šírka: 89 mm Výška: 89 mm Hĺbka: 10 mm
Trieda filtra	podľa STN EN 779: G2 podľa STN EN ISO 16890: ISO Coarse 50%
Balenie	50 pc(s).
Netto hmotnosť	0,05 kg
Brutto hmotnosť	0,164 kg
Číslo colnej sadzby	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	SK fleecová filtračná vložka, pre filtroventilátor SK 3237.7xx/3237.3xx, ŠxVxH: 89 x 89 x 10 mm

## Approvals

# Approvals

---

Approvals

CSA

UR + C-UR (recognized)