

Rittal – The System.

Faster – better – everywhere.



SK 3237.067

Filtračná vložka z netkanej textílie

State: 4.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.067 - Filtračná vložka z netkanej textílie

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.



Features

Obj. č.	SK 3237.067
Prevedenie	pre ventilátory s filtrom EMC
Materiál	Umelé vlákna s vrstvou zliatiny medi, niklu a chrómu
Farba	Antracitová
Poznámka	Výkonové parametre, stupeň krytia a certifikácie prístrojov sú zaručené len v spojení s originálnymi filtračnými vložkami Rittal.
Vhodný pre obj. č.	3237.4xx/3237.8xx
Rozmery	Šírka: 92 mm Výška: 92 mm Hĺbka: 10 mm
Trieda filtra	podľa STN EN 779: G2 podľa STN EN ISO 16890: ISO Coarse 50%
Balenie	5 pc(s).
Netto hmotnosť	0,005 kg
Brutto hmotnosť	0,01 kg
Číslo colnej sadzby	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Features

Popis výrobku

SK fleecová filtračná vložka, pre EMC filtroventilátory SK
3237.8xx/3237.4xx, ŠxVxH: 92 x 92 x 10 mm

Approvals

Approvals

CSA
UR + C-UR (recognized)