

# Rittal – The System.

Faster – better – everywhere.



## SK 3238.025 Skladany filter

State: 10.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3238.025 - Skladaný filter pre ventilátory s filtrom, chladiace jednotky a chillery

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.

## Features

Obj. č.	SK 3238.025
Prevedenie	pre ventilátory s filtrom/výstupné mriežky
Materiál	Skladaný filter: na báze polyesteru, fúkaného polykarbonátu Absorbér: 100% polyester
Farba	biela
Poznámka	Nie je vhodný pre EMC ventilátory s filtrom/výstupné mriežky.
Vhodný pre obj. č.	3238.3xx 3238.7xx
Rozmery	Šírka: 114 mm Výška: 114 mm Hĺbka: 14 mm
Rozmery absorpčnej podložky	Šírka: 120 mm Výška: 120 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55 in fan-and-filter units/outlet filters
Balenie	5 pc(s).
Netto hmotnosť	0,1 kg
Brutto hmotnosť	0,113 kg
Číslo colnej sadzby	56039390
ETIM 9	EC002513

## Features

---

ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	SK skladaný filter IP55, pre filtroventilátor/výstupná mriežka 3238.7xx/3238.3xx, ŠxVxH: 114x114x14 mm

---

## Approvals

---

Approvals	CSA UR + C-UR (recognized)
-----------	-------------------------------

---