


Rittal – The System.

Faster – better – everywhere.



SK 3238.080

Ochranný kryt proti striekajúcej vode

State: 10.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.080 - Ochranný kryt proti striekajúcej vode pre zvýšenie stupňa krytia

Particularly for applications in the food industry, the hose-proof hood prevents the ingress of damp. The protection category IP 56 is achieved in conjunction with a standard filter.



Features

Obj. č.	SK 3238.080
Materiál	Nerezová oceľ AISI304 – 1.4301 (V2A) Silikón
Vhodný pre obj. č.	3238....
Rozmery	Šírka: 176 mm Výška: 245 mm Hĺbka: 55 mm
Stupeň krytia NEMA	NEMA 1 NEMA 12 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Stupeň krytia IP podľa normy IEC 60 529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat
Balenie	1 pc(s).
Netto hmotnosť	1,23 kg
Brutto hmotnosť	1,358 kg
Číslo colnej sadzby	73269098

Features

ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405
Popis výrobku	SK kryt proti striekajúcej vode, pre SK 3238.... ŠxVxH 176 x 245 x 55 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
-----------	---