


# Rittal – The System.

Faster – better – everywhere.



## SK 3240.080

# Ochranný kryt proti striekajúcej vode

State: 17.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3240.080 - Ochranný kryt proti striekajúcej vode pre zvýšenie stupňa krytia

Particularly for applications in the food industry, the hose-proof hood prevents the ingress of damp. The protection category IP 56 is achieved in conjunction with a standard filter.



## Features

Obj. č.	SK 3240.080
Materiál	Nerezová oceľ AISI304 – 1.4301 (V2A) Silikón
Vhodný pre obj. č.	3240.... 3241....
Rozmery	Šírka: 282 mm Výška: 390 mm Hĺbka: 85 mm
Stupeň krytia NEMA	NEMA 1 NEMA 12 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Stupeň krytia IP podľa normy IEC 60 529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat
Balenie	1 pc(s).
Netto hmotnosť	2,5 kg
Brutto hmotnosť	2,887 kg

# Features

---

Číslo colnej sadzby	73269098
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405
Popis výrobku	SK kryt proti striekajúcej vode, za SK 3240..../3241.... ŠxVxH 282 x 390 x 85 mm

# Approvals

---

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
-----------	---