

Rittal – The System.

Faster – better – everywhere.



SK 3240.200 Výstupná mriežka

State: 7.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3240.200 - Výstupná mriežka Štandardné

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



Features

Obj. č.	SK 3240.200
Materiál	ABS
Farba	RAL 7035
Rozsah dodávky	Výstupná mriežka Filtračná vložka z netkanej textílie
Montážny výrez	Šírka výrezu: 224 mm Výška výrezu: 224 mm
Vhodný pre obj. č.	3240.1xx/3240.5xx/3241.1xx/3241.5xx
Rozmery	Šírka: 255 mm Výška: 255 mm Hĺbka: 25 mm
Stupeň krytia NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter/pleated filter and hose-proof hood
Stupeň krytia IP podľa normy IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Balenie	1 pc(s).

Features

Netto hmotnosť	0,56 kg
Brutto hmotnosť	0,582 kg
Číslo colnej sadzby	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	Výstupný mriežka pre SK, štandard, ŠxVxH: 255 x 255 x 25 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity