


Rittal – The System.

Faster – better – everywhere.



SK 3241.118

Ventilátory s filtrom TopTherm

State: 1.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3241.118 - Ventilátory s filtrom TopTherm

Complete fan unit for tool-free mounting on surfaces. Air throughput from 20 - 900 m³/h, standard protection category IP 54.

Features

Obj. č.	SK 3241.118
Prevedenie	nástenná montáž
Product modification	The cover for the connection clamp has not been part of the TopTherm filter fans since May 2024. In testing, it proved not to be necessary to meet the standard, and affects neither function nor operational reliability.
Farba	RAL 9005
Rozsah dodávky	Kompletné zariadenie, pripravené na zapojenie a okamžité použitie, vrátane filtračnej vložky
Ventilátor	Diagonal, shaded pole motor
Množstvo vzduchu pri voľnom prúdení (so skladanými filtrom)	Pri 50 Hz: 272 m ³ /h Pri 60 Hz: 272 m ³ /h
Aerodynamický výkon, voľné prúdenie (s filtrom z netkanej textílie)	Pri 50 Hz: 225 m ³ /h Pri 60 Hz: 245 m ³ /h
Aerodynamický výkon s výstupným filtrom vrátane filtračnej vložky z netkanej textílie (počet x objednávacie číslo)	1 x 3240208: 171/182 m ³ /h 2 x 3240208: 200/217 m ³ /h
Menovité prevádzkové napätie	115 V, 1~, 50 Hz/60 Hz
Menovitý elektrický príkon Pel	Pri 50 Hz: 40 W Pri 60 Hz: 42 W
Menovitý prúd max.	Pri 50 Hz: 0,52 A Pri 60 Hz: 0,48 A
Rozmery	Šírka: 255 mm Výška: 255 mm

Features

Inštaláčn hbka	107 mm
Montžny vrez	Šrka vrezu: 224 mm Vška vrezu: 224 mm
Stupe krytia IP poda normy IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Stupe krytia NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter/pleated filter and hose-proof hood
Predraden istenie	Isti/tavn poistka: 4 A
Poznmka	Pre zvyšenie aerodynamickho vkonu je možne volitene pouit skladan filter (vid charakteristick krivku). Je možne ho pouit pre ventiltory s filtrom, strene ventiltory aj pre vstupne filtre. Pri ventiltore s filtrom 3237.XXX je elektrick pripojenie prevedene pomocou 2 vodiov (džka cca 300 mm), ktore s sasou zariadenia. Pri všetkch ostatnch ventiltoroch s filtrom pomocou pruinovej svorky.
ivotnos ventiltora (L10, 40 °C)	Pri 50 Hz: 61.000 h Pri 60 Hz: 60.000 h
Rozsah prevdzkovch teplt	-30 °C...55 °C
Rozsah skladovacch teplt	-30 °C...70 °C
Hladina akustickho tlaku	Pri 50 Hz: 54 dB(A) Pri 60 Hz: 56 dB(A)
Balenie	1 pc(s).
Netto hmotnos	2,2 kg
Brutto hmotnos	2,36 kg
slo colnej sadzby	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Features

Popis výrobku

SK filtroventilátor TopTherm, 225/245 m³/h, 115 V, 1~, 50/60 Hz,
ŠxVxH: 255 x 255 x 25 mm

Approvals

Approvals

30 - KC Korea
UL + C-UL - FTTA
UR + C-UR (recognized)

Explanations

Declaration of conformity
Declaration of conformity UK