

Rittal – The System.

Faster – better – everywhere.



SK 3243.300

Blue e+ výstupný filter

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3243.300 - Blue e+ výstupný filter

The outlet filter is used in conjunction with the corresponding fan-and-filter unit to dissipate heat loss from enclosures, ventilate the enclosure and protect temperature-sensitive components. This is achieved through the direct infeed of ambient air, the temperature of which must be lower than the permissible internal temperature of the enclosure.



Features

Obj. č.	SK 3243.300
Prevedenie	nástenná montáž
Výhody	Jednoduchá výmena filtra vďaka novému otváraciemu mechanizmu na lamelovej mriežke Rýchlejšia montáž na skriňu vďaka optimalizovaným zaklapávacím háčikom Montáž bez použitia náradia
Materiál	Plast
Farba	RAL 7035
Rozsah dodávky	Výstupná mriežka Skladaný filter
Montážny výrez	Šírka výrezu: 292 mm Výška výrezu: 292 mm
Vhodný pre obj. č.	SK 3243.7xx/3243.9xx/3244.7xx/3244.9xx/3245.9xx

Features

Rozmery	Šírka: 323 mm Výška: 323 mm Hĺbka: 44,7 mm
Stupeň krytia NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-proof hood
Stupeň krytia IP podľa normy IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Balenie	1 pc(s).
Netto hmotnosť	0,956 kg
Brutto hmotnosť	0,956 kg
Číslo colnej sadzby	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	Výstupná mriežka SK Blue e+, pre filtroventilátor 3243.7xx/3243.9xx/3244.7xx/3244.9xx/3245.9xx, ŠxV 323 x 323 mm, RAL 7035

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
-----------	---