


Rittal – The System.

Faster – better – everywhere.



SK 3285.910 Kovový filter

State: 28.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3285.910 - Kovový filter pre chladiace prístroje, modulárne chladiace dvere, výmenníky tepla vzduch- vzduch a chladiče

We recommend the use of washable metal filters, particularly in environments with dusty or oily ambient air. If air or steam condenses on the metal surfaces, any particles that may be present will adhere to the metal and are easily washed out with water or grease-dissolving detergents.

Features

Obj. č.	SK 3285.910
Materiál	Hliník
Vhodný pre obj. č.	3186.93x / 3486.93x 3187.93x / 3487.93x 3188.94x / 3488.94x 3189.94x / 3489.94x 3186.63x / 3486.63x 3187.63x / 3487.63x 3188.64x / 3488.64x 3189.64x / 3489.64x 3334.400 / 3434.400 3334.450 / 3434.450
Rozmery	Šírka: 380 mm Výška: 355 mm Hĺbka: 10 mm
Balenie	1 pc(s).
Netto hmotnosť	0,374 kg
Brutto hmotnosť	0,424 kg
Číslo colnej sadzby	84219990
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Features

Popis výrobku

SK kovový filter, pre chladiace jednotky a chiller, pre SK
3186/87.930, 3188/89.940, 3334.400, ŠxVxH 380 x 358 x 10 mm