

Rittal – The System.

Faster – better – everywhere.



SK 3311.360

Kondenzátorová jednotka

State: 2.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.360 - Kondenzátorová jednotka pre LCP DX

The condenser units are necessary for operating refrigerant-based LCPs. Depending on the version, the units have an external condenser and fan, or additionally a free cooler. The variant with free cooler is needed for the combination variant LCP DX/FC. The units are suitable for roof and wall mounting.

Features

Obj. č.	SK 3311.360
Prevedenie	Kondenzátor
Materiál	Oceľový plech, s nástrekom
Povrch	Štruktúrovaná prášková farba, pozinkované
Farba	RAL 9003
Rozsah dodávky	Základná jednotka Vrátane montážneho materiálu
Max. chladiaci výkon	12 kW
Regulácia teploty	Speed-controlled fan
Chladiace médium/chladivo	Chladivo: R410A Chladiace médium: -
Rozmery	Šírka: 1.303 mm Výška: 915 mm Hĺbka: 620 mm
Celkový chladiaci výkon / počet ventilátorov	2
Menovité prevádzkové napätie	230 V, 1~, 50 Hz/60 Hz
Balenie	1 pc(s).
Netto hmotnosť	38 kg
Brutto hmotnosť	64 kg
Číslo colnej sadzby	84189910
ETIM 9	EC002515

Features

ETIM 8	EC002515
ECLASS 8.0	27180712
Popis výrobku	Vzduchom chladený kondenzátor pre LCP Rack/Inline DX, pre montáž na strechu/stenu, napájanie: 230 V, 1~, 50/60 Hz, ŠxVxH: 1308x928x620 mm, RAL 9003
