

Rittal – The System.

Faster – better – everywhere.



SK 3312.815

Dvere z ocelového plechu

State: 28.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3312.815 - Dvere z ocelového plechu pre nástennú chladiacu jednotku Blue e+ IT

For mounting the wall-mounted cooling unit. The cut-out in the door is arranged so that the wall-mounted cooling unit is positioned centrally on the door.

Features

| | |
|---------------------|--|
| Obj. č. | SK 3312.815 |
| Materiál | Ocelový plech |
| Povrch | S nástrekom |
| Farba | RAL 7035 |
| Rozsah dodávky | Dvere z ocelového plechu, vzadu Komfortná rukoväť pre profilovú cylindrickú polvložku s bezpečnostným zámkom 3524 E Vrátane upevňovacieho materiálu, (s uzatváracími dielmi, bez pántovov) |
| Vhodný pre obj. č. | 3312.810 / 3412.810 3186.x3x / 3486.x3x 3187.x3x / 3487.x3x 3188.x4x / 3488.x4x 3189.x4x / 3489.x4x |
| Rozmery | Šírka: 600 mm Výška: 2.000 mm |
| Vhodné pre | Typ skrine: VX IT VX |
| Balenie | 1 pc(s). |
| Netto hmotnosť | 13 kg |
| Brutto hmotnosť | 15 kg |
| Číslo colnej sadzby | 94039910 |
| ETIM 9 | EC002510 |
| ETIM 8 | EC000744 |

Features

ECLASS 8.0

27182405

Popis výrobku

Dvere z ocelového plechu SK IT, pre VX IT, s montážnym výrezom pre chladiace jednotky 3312.810/3412.810, ŠxH: 600x2000 mm, RAL 7035