


Rittal – The System.

Faster – better – everywhere.



SK 3322.700

Filtračná vložka z netkanej textílie

State: 10.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3322.700 - Filtračná vložka z netkanej textílie

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Obj. č.	SK 3322.700
Prevedenie	pre ventilátory s filtrom
Materiál	Chemické vlákna
Poznámka	Nie je vhodný pre EMC ventilátory s filtrom/výstupné mriežky.
Vhodný pre obj. č.	3238....
Rozmery	Šírka: 120 mm Výška: 120 mm Hĺbka: 11 mm
Trieda filtra	podľa STN EN 779: G2 podľa STN EN ISO 16890: ISO Coarse 50%
Balenie	5 pc(s).
Netto hmotnosť	0,01 kg
Brutto hmotnosť	0,013 kg
Číslo colnej sadzby	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	SK náhradná filtračná vložka, pre filtroventilátor, pre SK 3238.... ŠxVxH 120 x 120 x 12 mm

Approvals

Approvals

Approvals

CSA

UR + C-UR (recognized)