


Rittal – The System.

Faster – better – everywhere.



SK 3342.024

Zásuvné a tlačné ventilátory pre 482,6 mm (19")

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3342.024 - Zásuvné a tlačné ventilátory pre 482,6 mm (19") Množstvo vzduchu 320–480 m³/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

Features

| | |
|--|--|
| Obj. č. | SK 3342.024 |
| Farba | RAL 7035 |
| Rozsah dodávky | Kompletné zariadenie pripravené na okamžité pripojenie a použitie Vrátane svorkovnice a upevňovacieho materiálu |
| Aerodynamický výkon (pri voľnom prúde vzduchu) | 480 m ³ /h |
| Poznámka k obj. č. | Dodacia lehota na vyžiadanie |
| Menovité prevádzkové napätie | 24 V (DC) |
| Menovitý prúd max. | pri DC: 0,74 A |
| Predradené istenie | Istič/tavná poistka: 6 A |
| Rozmery | Šírka: 482,6 mm Výška: 44 mm Hĺbka: 200 mm |
| Osová vzdialenosť ventilátorov | 105 mm |
| Počet ventilátorov | 3 |
| Hladina akustického tlaku | pri DC: 51 dB(A) |
| Rozsah prevádzkových teplôt | -10 °C...55 °C |
| Balenie | 1 pc(s). |
| Netto hmotnosť | 1,75 kg |
| Brutto hmotnosť | 1,86 kg |
| Číslo colnej sadzby | 84145915 |
| ETIM 9 | EC000320 |

Features

| | |
|---------------|--|
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Popis výrobku | SK zásuvný ventilátor, pre 482,6 mm (19"), 480 m ³ /h, 24 V (DC), ŠxVxH: 482,6 x 44 x 200 mm |

Approvals

| | |
|--------------|-------------------------------|
| Approvals | UR + C-UR (recognized) VDE |
| Explanations | Declaration of conformity |
