

# Rittal – The System.

Faster – better – everywhere.



## SK 3357.100

## Vodiaci rám

State: 2.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3357.100 - Vodiaci rám pre zásuvné ventilátory Vario

Guide frame for Vario rack-mounted fan: Installation directly in the subrack or using two mounting brackets on the 482.6 mm (19") mounting angles.



## Features

Obj. č.	SK 3357.100
Rozsah dodávky	Vodiaci rám Vrátane konektora a zapojeného prívodného kábla Montážny uholník pre voliteľnú montáž na 482,6 mm (19") upevňovaciu rovinu Upevňovací materiál
Dĺžka prívodného kábla	3 m
Vhodný pre obj. č.	3352.500
Elektrické pripojenie	24 V DC 115 - 230 V
Balenie	1 pc(s).
Netto hmotnosť	1,395 kg
Brutto hmotnosť	1,52 kg
Číslo colnej sadzby	84149000
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Popis výrobku	Rám SK, pre zásuvný ventilátor Vario SK 3352.500, pre 24 V (DC), 115-230 V