

Rittal – The System.

Faster – better – everywhere.



SV 3452.500

Svorky na pripojenie vodičov

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3452.500 - Svorky na pripojenie vodičov

For connecting round conductors and laminated copper bars.

Features

Obj. č.	SV 3452.500
Materiál	Oceľový plech
Povrch	Pozinkované, pasivované
Priestor na upevnenie lamelových medených prípojnic (Š x V)	10,5 x 11 mm
Poznámka	Pri použití jemne alebo veľmi jemne lanených vodičov je nutné použiť lisovacie dutinky.
Pripojenie okrúhlych vodičov	16 - 50 mm ²
Pre hrúbku prípojnic	5 mm
Balenie	15 pc(s).
Netto hmotnosť	0,81 kg
Brutto hmotnosť	1,004 kg
PCF per pack (cradle-to-gate)	3,9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Popis výrobku	Pripojovacie svorky SV, 16-50 mm ² , priestor svoriek ŠXV: 10,5x11 mm, pre hrúbku prípojnice 5 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK
