

**Rittal – The System.**

Faster – better – everywhere.



**SV 3454.500**

**Svorky na pripojenie vodičov**

State: 22.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3454.500 - Svorcky na pripojenie vodičov

For connecting round conductors and laminated copper bars.

## Features

Obj. č.	SV 3454.500
Materiál	Oceľový plech
Povrch	Pozinkované, pasivované
Priestor na upevnenie lamelových medených prípojnic (Š x V)	22,5 x 20 mm
Poznámka	Pri použití jemne alebo veľmi jemne lanených vodičov je nutné použiť lisovacie dutinky.
Pripojenie okrúhlych vodičov	70 - 185 mm <sup>2</sup>
Pre hrúbku prípojnic	5 mm
Balenie	15 pc(s).
Netto hmotnosť	1,95 kg
Brutto hmotnosť	1,982 kg
PCF per pack (cradle-to-gate)	7,6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Popis výrobku	Pripojovacie svorky SV, 70-185 mm <sup>2</sup> , priestor svoriek ŠXV: 22,5x20 mm, pre hrúbku prípojnice 5 mm

# Approvals

---

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

---