

# Rittal – The System.

Faster – better – everywhere.



## SV 3456.500

# Svorky na pripojenie vodičov

State: 22.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3456.500 - Svorky na pripojenie vodičov

For connecting round conductors and laminated copper bars.

## Features

|   |  |
|---|--|
| Obj. č.   | SV 3456.500  |
| Materiál  | Oceľový plech  |
| Povrch  | Pozinkované, pasivované  |
| Priestor na upevnenie lamelových medených prípojnic (Š x V) | 8 x 8 mm   |
| Poznámka  | Pri použití jemne alebo veľmi jemne lanených vodičov je nutné použiť lisovacie dutinky.                        |
| Pripojenie okrúhlych vodičov                                | 2,5 - 16 mm <sup>2</sup>   |
| Pre hrúbku prípojnic  | 10 mm  |
| Balenie   | 15 pc(s).  |
| Netto hmotnosť  | 0,405 kg   |
| Brutto hmotnosť   | 0,45 kg  |
| PCF per pack (cradle-to-gate)                               | 1,7 kg CO2 eq (Cat B)  |
| Note on PCF category  | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Číslo colnej sadzby   | 85369010   |
| ETIM 9  | EC000001   |
| ETIM 8  | EC000001   |
| ECLASS 8.0  | 27141146   |
| Popis výrobku   | Pripojovacie svorky SV, 2,5-16 mm <sup>2</sup> , priestor svoriek ŠXV: 8x8 mm, pre hrúbku prípojnice 10 mm     |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---