

# Rittal – The System.

Faster – better – everywhere.



## SV 3584.020

## Prípojnice CUPONAL

State: 11.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3584.020 - Přípojnice CUPONAL

Copper-coated aluminium busbar



## Features

Obj. č.	SV 3584.020
Materiál	Hliník Meď
Menovitý prúd max.	328 A
Poznámka	Menovitý prúd je odvodený pri teplote prípojnice 65 °C a teplote okolitého prostredia 35 °C Graf korekčného činiteľa podľa normy DIN EN 43 671 Dĺžku je možné individuálne skrátiť.
Normy	DIN EN 13 601
Prierez	30 mm x 5 mm
Rozmery	Dĺžka: 2.400 mm
Balenie	6 pc(s).
Netto hmotnosť	8,52 kg
Brutto hmotnosť	9,02 kg
Podiel medi (kg / ks)	0,52
Číslo colnej sadzby	76042990
ETIM 9	EC001522

# Features

---

ETIM 8	EC001522
ECLASS 8.0	27370303
Popis výrobku	SV přípojnice CUPONAL, ŠxV: 30x5 mm, D: 2400 mm

---

# Approvals

---

Explanations	Declaration of conformity
	Declaration of conformity UK