


Rittal – The System.

Faster – better – everywhere.



HD 4000.240 Nivelačné nohy HD

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.240 - Nivelačné nohy HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

Features

Obj. č.	HD 4000.240
Prevedenie	bez upevnenia k podlahe
Výhody	Minimalizovanie sanácie vďaka kompletne zakrytému a trvalo uzavretému závit Vyrovnávanie sklonu podlahy až do uhla 10° pomocou flexibilnej základne Možnosť radového spojenia aj pri šikmých podlahách vďaka veľkému rozsahu nivelácie Certifikácia podľa noriem 3-A Sanitary
Materiál	Nerezová oceľ 1.4301 (AISI 304)
Rozsah dodávky	Vrátane upevňovacieho materiálu a tesnenia
Zaťažiteľnosť	Max. 7000 N statická záťaž na každú nivelačnú nohu
Rozmery	Závit: M12
Vhodné pre	Typ skrine: HD compact enclosure VX VX SE TS
Rozsah nivelácie	122 - 175 mm
Balenie	4 pc(s).
Netto hmotnosť	2 kg
Brutto hmotnosť	2,342 kg
Číslo colnej sadzby	73181900
ETIM 9	EC002622
ETIM 8	EC002622
ECLASS 8.0	27189263

Features

Popis výrobku

HD nivelačná noha, bez montáže na podlahu, nerezová oceľ, 1.4301