

Rittal – The System.

Faster – better – everywhere.



AS 4051.542

Dutinky

State: 25.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.542 - Dutinky na páske

With plastic collar.

Features

Obj. č.	AS 4051.542
Technické údaje	Teplotne odolné do 105 °C
Materiál	E-Cu, galvanicky pocínované Plastový lem: polypropylén
Farba	žltá
Dĺžka	8 mm
Prierez	18
Vnútorň priemer	3,5 mm
Farebné značenie Rittal	Yes
Pre prierez	1 mm ²
Multinorm	Yes
Poznámka	Certifikácia UL v spojení so zodpovedajúcimi nástrojmi, napr. krimpovacími strojmi.
Spôsob dodania	Taped
Balenie	4 000 pc(s).
Netto hmotnosť	4 kg
Brutto hmotnosť	0,568 kg
Číslo colnej sadzby	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Popis výrobku	Dutinky 1,0 mm ² x 8 mm AWG 18 Multinorm, V=4 000 kusov Farba: žltá, forma dodávky: na páske (podľa farebného kódu Rittal), 1,0 mm ²

Approvals

Approvals

UL + C-UL (listed)