

Rittal – The System.

Faster – better – everywhere.



AS 4051.544

Dutinky

State: 2.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.544 - Dutinky na páske

With plastic collar.

Features

Obj. č.	AS 4051.544
Technické údaje	Teplotne odolné do 105 °C
Materiál	E-Cu, galvanicky pocínované Plastový lem: polypropylén
Farba	biela
Dĺžka	10 mm
Prierez	20
Vnútorň priemer	2,9 mm
Pre prierez	0,5 mm ²
Farebné značenie DIN	Yes
Multinorm	Yes
Poznámka	Certifikácia UL v spojení so zodpovedajúcimi nástrojmi, napr. krimpovacími strojmi.
Spôsob dodania	Taped
Balenie	4 000 pc(s).
Netto hmotnosť	4 kg
Číslo colnej sadzby	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Popis výrobku	Dutinky 0,5 mm ² x 10 mm AWG 20 Multinorm, V=4 000 kusov Farba: biela, forma dodávky: na páske (podľa farebného kódu DIN), 0,5 mm ²

Approvals

Approvals

UL + C-UL (listed)