

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.545

## Dutinky

State: 22.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.545 - Dutinky na páske

With plastic collar.

## Features

Obj. č.	AS 4051.545
Technické údaje	Teplotne odolné do 105 °C
Materiál	E-Cu, galvanicky pocínované Plastový lem: polypropylén
Farba	šedá
Dĺžka	10 mm
Prierez	18
Vnútorň priemer	3,4 mm
Pre prierez	0,75 mm <sup>2</sup>
Farebné značenie DIN	Yes
Multinorm	Yes
Poznámka	Certifikácia UL v spojení so zodpovedajúcimi nástrojmi, napr. krimpovacími strojmi.
Spôsob dodania	Taped
Balenie	4 000 pc(s).
Číslo colnej sadzby	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Popis výrobku	Dutinky 0,75 mm <sup>2</sup> x 10 mm AWG 18 Multinorm, V = 4 000 kusov Farba: šedá, forma dodávky: na páske (podľa farebného kódu DIN), 0,75 mm <sup>2</sup>

# Approvals

---

Approvals

UL + C-UL (listed)