


Rittal – The System.

Faster – better – everywhere.



AS 4051.577

Dutinky

State: 27.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.577 - Dutinky voľné

With plastic collar.

Features

Obj. č.	AS 4051.577
Technické údaje	Teplotne odolné do 105 °C
Materiál	E-Cu, galvanicky pocínované Plastový lem: polypropylén
Farba	biela
Dĺžka	8 mm
Prierez	18
Vnútorň priemer	3,4 mm
Farebné značenie Rittal	Yes
Multinorm	Yes
Poznámka	Certifikácia UL v spojení so zodpovedajúcimi nástrojmi, napr. krimpovacími strojmi. Pre individuálne poradenstvo kontaktujte prosím odborného poradcu spoločnosti Rittal.
Spôsob dodania	Loose
Balenie	500 pc(s).
Netto hmotnosť	0,5
Číslo colnej sadzby	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Popis výrobku	Dutinky pre spracovanie vodiča 0,75 mm ² , biele, voľné, 8 mm

Approvals

Approvals

UL + C-UL (listed)

UR