

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.792

## Dutinky

State: 27.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.792 - Dutinky voľné

With plastic collar.

## Features

|                     |  |
|---------------------|--|
| Obj. č.             | AS 4051.792  |
| Technické údaje     | Teplotne odolné do 105 °C  |
| Materiál            | E-Cu, galvanicky pocínované<br>Plastový lem: polypropylén  |
| Farba               | svetlo modrá   |
| Dĺžka               | 10 mm  |
| Prierez             | 18   |
| Vnútorň priemer     | 3,4 mm   |
| Multinorm           | Yes  |
| Poznámka            | Certifikácia UL v spojení so zodpovedajúcimi nástrojmi, napr. krimpovacími strojmi.<br>Pre individuálne poradenstvo kontaktujte prosím odborného poradcu spoločnosti Rittal. |
| Spôsob dodania      | Loose  |
| Balenie             | 500 pc(s).   |
| Netto hmotnosť      | 0,5  |
| Číslo colnej sadzby | 85369010   |
| ETIM 9              | EC000005   |
| ETIM 8              | EC000005   |
| ECLASS 8.0          | 36659290   |
| Popis výrobku       | Dutinky pre spracovanie vodiča 0,75 mm <sup>2</sup> , svetlomodré, voľné, 10 mm  |

# Approvals

---

Approvals

UL + C-UL (listed)

UR