


# Rittal – The System.

Faster – better – everywhere.



## AS 4052.032 Skrutkovače

State: 25.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4052.032 - Skrutkovače neizolovaný

Ergonomic screwdriver which adapts perfectly to the hand, thereby minimising the force required.



## Features

Obj. č.	AS 4052.032
Prevedenie	pre skrutky s krížovou drážkou Phillips
Výhody	Hlava rukoväte s ochranou proti skotúľaniu a jasným označením typu skrutkovača Na čierne morená špička hrotu pre zachovanie presnosti a lícovania Optimálne uchopenie rukoväte umožňujúce vyšší krútiaci moment a dlhšiu prácu bez únavy
Materiál	Hrot: zliatina chrómu, molybdénu a vanádu Jadro rukoväte: tvrdý plast Telo rukoväte: elastický, vysoko flexibilný plast
Farba	Rukoväť: antracitová a Rittal Power Pink
Ø hrotu	6 mm
Dĺžka hrotu	100 mm
Typ hrotu	PH 2
Priemer rukoväte	36 mm
Dĺžka rukoväte	106 mm
Balenie	1 pc(s).
Netto hmotnosť	0,09 kg
Brutto hmotnosť	0,097 kg

# Features

Číslo colnej sadzby	82054000
ETIM 9	EC000144
ETIM 8	EC000144
ECLASS 8.0	21040406
Popis výrobku	Skrutkovač, neizolovaný, hrot: PH 2