


Rittal – The System.

Faster – better – everywhere.



AS 4052.056 Skrutkovače

State: 5.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.056 - Skrutkovače neizolovaný

Ergonomic screwdriver which adapts perfectly to the hand, thereby minimising the force required.



Features

Obj. č.	AS 4052.056
Prevedenie	pre TX
Výhody	Hlava rukoväte s ochranou proti skotúľaniu a jasným označením typu skrutkovača Na čierne morená špička hrotu pre zachovanie presnosti a lícovania Optimálne uchopenie rukoväte umožňujúce vyšší krútiaci moment a dlhšiu prácu bez únavy
Materiál	Hrot: zliatina chrómu, molybdénu a vanádu Jadro rukoväte: tvrdý plast Telo rukoväte: elastický, vysoko flexibilný plast
Farba	Rukoväť: antracitová a Rittal Power Pink
Ø hrotu	5 mm
Dĺžka hrotu	100 mm
Typ hrotu	TX 25
Priemer rukoväte	36 mm
Dĺžka rukoväte	106 mm
Balenie	1 pc(s).
Netto hmotnosť	0,08 kg
Brutto hmotnosť	0,087 kg

Features

Číslo colnej sadzby	82054000
ETIM 9	EC000801
ETIM 8	EC000801
ECLASS 8.0	21040406
Popis výrobku	Skrutkovač, neizolovaný, hrot: TX 25