


Rittal – The System.

Faster – better – everywhere.



AS 4052.104 Skrutkovače

State: 19.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.104 - Skrutkovače izolovaných

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

Obj. č.	AS 4052.104
Prevedenie	S ochrannou izoláciou 1000 V pre skrutky s jednou drážkou
Výhody	Malá vynakladaná sila vďaka ergonomicky tvarovanej rukoväti Hlava rukoväte s ochranou proti skotúľaniu a jasným označením typu skrutkovača Na čierno morená špička hrotu pre zachovanie presnosti a lícovania Rukoväť o 30 % a izolácia až o 50 % štíhlejšia ako pri porovnateľnom náradí Optimálne uchopenie rukoväte umožňujúce vyšší krútiaci moment a dlhšiu prácu bez únavy
Materiál	Hrot: zliatina chrómu, molybdénu a vanádu Jadro rukoväte: tvrdý plast Telo rukoväte: elastický, vysoko flexibilný plast
Farba	Rukoväť: antracitová a Rittal Power Pink
Ø hrotu	4 mm
Dĺžka hrotu	100 mm
Hrot (šírka x hrúbka)	4 x 0,8 mm
Typ hrotu	SL
Priemer rukoväte	25 mm
Dĺžka rukoväte	105 mm
Normy	IEC 60 900
Balenie	3 pc(s).
Netto hmotnosť	0,135
Číslo colnej sadzby	82054000
ETIM 9	EC000144

Features

ETIM 8	EC000158
ECLASS 8.0	21040406
Popis výrobku	Skrutkovač, izolovaný, hrot: SL 4 x 0,8 mm
