

Rittal – The System.

Faster – better – everywhere.



AS 4054.000 Krimповacie kliešte

State: 28.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.000 - Krimpovacie kliešte pre dutinky

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



Features

Obj. č.	AS 4054.000
Prevedenie	zahnuté
Výhody	Minimálna vynaložená sila pri veľkých prierezoch vodičov Stabilne vysoko kvalitné lisovanie Značené pozície pre presné spracovanie príslušného prierezu Uvoľniteľná západka
Materiál	Vysoko kvalitná špeciálna nástrojová oceľ
Povrch	Matný, chrómovaný
Farba	Rukoväť: antracitová a Rittal Power Pink
Lisovanie	Trapezoid crimp
Smer zavedenia kábla	bočné
Rozmery	Výška: 59 mm Dĺžka: 198 mm
Prierez	24 - 10
Pre prierez	0,25 - 6 mm ²
Balenie	1 pc(s).
Netto hmotnosť	0,439 kg
Brutto hmotnosť	0,449 kg

Features

Číslo colnej sadzby	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Popis výrobku	Lisovacie kliešte 0,25 - 6 mm ² , lichobežníkové lisovanie, pre dutinky s izolačnou manžetou a bez nej