

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.002

### Krimповacie kliešte

State: 27.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.002 - Krimpovacie kliešte pre dutinky

Crimping tool for square or hexagonal compression, for processing wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.

## Features

|                      |  |
|----------------------|--|
| Obj. č.              | AS 4054.002  |
| Prevedenie           | priame   |
| Výhody               | Minimálna vynaložená sila pri veľkých prierezoch vodičov<br>Stabilne vysoko kvalitné lisovanie<br>Uvoľniteľná západka<br>Samoregulačné |
| Materiál             | Vysoko kvalitná špeciálna nástrojová oceľ  |
| Povrch               | Matný, chrómovaný  |
| Farba                | Rukoväť: RAL 7016 a RAL 35745  |
| Lisovanie            | Square crimp   |
| Smer zavedenia kábla | bočné  |
| Rozmery              | Dĺžka: 176 mm  |
| Prierez              | 26 - 8   |
| Pre prierez          | 0,14 - 10 mm <sup>2</sup>  |
| Balenie              | 1 pc(s).   |
| Netto hmotnosť       | 0,4 kg   |
| Brutto hmotnosť      | 0,449 kg   |
| Číslo colnej sadzby  | 82032000   |
| ETIM 9               | EC000168   |
| ETIM 8               | EC000168   |
| ECLASS 8.0           | 21043811   |
| Popis výrobku        | AS lisovacie kliešte štvorcové, pre prierez 0,14 - 10 mm <sup>2</sup>  |