


Rittal – The System.

Faster – better – everywhere.



AS 4054.003 Krimповacie kliešte

State: 27.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.003 - Krimpovacie kliešte pre dutinky

Crimping tool for square or hexagonal compression, for processing wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.

Features

Obj. č.	AS 4054.003
Prevedenie	priame
Výhody	Minimálna vynaložená sila pri veľkých prierezoch vodičov Stabilne vysoko kvalitné lisovanie Uvoľniteľná západka Samoregulačné
Materiál	Vysoko kvalitná špeciálna nástrojová oceľ
Povrch	Matný, chrómovaný
Farba	Rukoväť: antracitová a Rittal Power Pink
Lisovanie	Hexagonal crimp
Smer zavedenia kábla	bočné
Rozmery	Dĺžka: 176 mm
Prierez	26 - 8
Pre prierez	0,14 - 10 mm ²
Balenie	1 pc(s).
Netto hmotnosť	0,4 kg
Brutto hmotnosť	0,455 kg
Číslo colnej sadzby	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Popis výrobku	AS lisovacie kliešte šesťhranné, pre prierez 0,14 - 10 mm ²