


Rittal – The System.

Faster – better – everywhere.



AS 4054.004 Krimpovacie kliešte

State: 9.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.004 - Krimpovacie kliešte pre dutinky

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



Features

Obj. č.	AS 4054.004
Prevedenie	priame
Výhody	Minimálna vynaložená sila pri veľkých prierezoch vodičov Stabilne vysoko kvalitné lisovanie Značené pozície pre presné spracovanie príslušného prierezu Uvoľniteľná západka
Materiál	Vysoko kvalitná špeciálna nástrojová oceľ
Povrch	Matný, chrómovaný
Farba	Rukoväť: antracitová a Rittal Power Pink
Lisovanie	WM crimp
Smer zavedenia kábla	bočné
Rozmery	Výška: 68 mm Dĺžka: 256 mm
Prierez	8 - 4
Pre prierez	10 - 25 mm ²
Balenie	1 pc(s).
Netto hmotnosť	0,66 kg
Brutto hmotnosť	0,69 kg
Číslo colnej sadzby	82032000

Features

ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Popis výrobku	Krimpovacie kliešte 10 - 25 mm ² , WM lisovanie, pre dutinky s izolačnou manžetou a bez nej